
E60119

Flexible coupling for encoders

COUPLING 19,2-4-6-28-KV



1 M3 x 10 - ISO 4762 (2x)
2 Depth der Klemmnabe

Mechanical data		
Weight	[g]	18.4
Dimensions	[mm]	Ø 19 / L = 28
Materials		aluminium
Tightening torque	[Nm]	tightening torque screws: 120 Ncm
Outer diameter D	[mm]	19
Inner diameter 1	[mm]	4
Inner diameter 2	[mm]	6
Depth of the clamping hub	[mm]	6.5
Clamping screw	[mm]	M3 x 10 - ISO 4762 (2x)
Length	[mm]	28
Max. revolution, mechanical	[U/min]	6000
Max. axial shaft misalignment	[mm]	± 0,4
Max. radial shaft misalignment	[mm]	± 0,25
Max. angular displacement	[°]	± 4,0

Remarks	
Remarks	The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C.
	The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation.
Pack quantity	1 pcs.