


TD2933



Temperature Transmitter with Display

TD-100FFEC02-A-ZVG/US



1 2" Clamp ISO 2852
EL = Installation length



EC 1935/2004

EHEDG Certified

FCM CN FCM JP



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1	
Measuring range	-50...150 °C	-58...302 °F
Communication interface	IO-Link	
Process connection	Clamp DN50 (2") DIN 32676 (ISO 2852)	
Installation length EL [mm]	100	

Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases

TD2933



Temperature Transmitter with Display

TD-100FFEC02-A-ZVG/US

Pressure rating	100 bar	10 MPa
Vacuum resistance	-1000 mbar	-0.1 MPa
Electrical data		
Operating voltage	[V]	18...32 DC; (cULus - Class 2 source required)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	2
Inputs / outputs		
Number of inputs and outputs	Number of analog outputs: 1	
Outputs		
Total number of outputs	1	
Output signal	analog signal; IO-Link; (configurable)	
Number of analog outputs	1	
Analog current output	[mA]	4...20
Max. load	[Ω]	300
Short-circuit protection	yes	
Overload protection	yes	
Measuring/setting range		
Probe length L	[mm]	100
Measuring range	-50...150 °C-58...302 °F	
Factory setting	0...300 °F	
Resolution		
Resolution of analog output	[K]	0.04
Resolution of display	[K]	0.28
Accuracy / deviations		
Precision analog output	[K]	± 0,3 + (± 0,1 % MS)
Temperature coefficient	0,1; (In case of deviation from the reference condition 25 °C)	
	[% of the span / 10 K]	
Reaction times		
Dynamic response T05 / T09	[s]	1 / 3
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
Profiles	Smart Sensor - SSP 0	Generic Profiled Sensor
Min. process cycle time	[ms]	2.3
Supported DeviceIDs	Type of operation	DeviceID
	default	376
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection	IP 67; IP 68; IP 69K	

TD2933



Temperature Transmitter with Display

TD-100FFEC02-A-ZVG/US

Tests / approvals			
EMC	DIN EN 61000-6-2		
	DIN EN 61000-6-3		
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN IEC 68-2-6	10 g (10...2000 Hz)	
Note on approval	Factory certificate available as download at www.factory-certificate.ifm		
UL approval	UL approval number	K001	
Mechanical data			
Weight	[g]	397	
Material	stainless steel (1.4404 / 316L); PEI; FKM		
Materials (wetted parts)	stainless steel (1.4404 / 316L) electropolished		
Process connection	Clamp DN50 (2") DIN 32676 (ISO 2852)		
Suitable for process connections in accordance with the standards	DIN 32676 series A (DIN)	clamp DN50	
	DIN 32676 series B (ISO)	clamp DN42,4, DN48,3	
	DIN 32676 series C (ASME BPE)	clamp 2"	
	ISO 2852	clamp DN40, DN51	
Surface characteristics Ra/Rz of the wetted parts	Ra < 0.8 µm		
Probe diameter	[mm]	6	
Installation length EL	[mm]	100	
Displays / operating elements			
Display			7-segment LED display, 4-digit
			Display unit / status, °C / °F
Remarks			
Remarks	MS = set measuring span		
	The values for accuracy apply to flowing water.		
Pack quantity	1 pcs.		
Electrical connection			
Connector: 1 x M12; coding: A; Contacts: 4			
			
Connection			
