
IGR207

Inductive full-metal sensor

IGB3008BBPKG/AM/SC/V4A/US-104



Product characteristics			
Electrical design			PNP
Output function			normally open
Sensing range	[mm]		8
Housing			threaded type
Dimensions	[mm]		M18 x 1 / L = 45
Application			
Special feature			Gold-plated contacts; Increased sensing range; Full-metal housing; Magnetic-field immune
Application			Use in welding applications
Pressure rating		100 bar	10 MPa
Note on pressure rating			sensing face
Magnetic-field immune			yes
Max. magnetic field immunity	[mT]		100
Electrical data			
Operating voltage	[V]		10...30 DC
Current consumption	[mA]		< 10
Protection class			III
Reverse polarity protection			yes
Outputs			
Electrical design			PNP
Output function			normally open
Max. voltage drop switching output DC	[V]		2.5
Permanent current rating of switching output DC	[mA]		100
Switching frequency DC	[Hz]		2
Short-circuit protection			yes
Overload protection			yes
Detection zone			
Sensing range	[mm]		8
Real sensing range Sr	[mm]		8 ± 10 %
Operating distance	[mm]		0...6.48
Increased sensing range			yes

IGR207

Inductive full-metal sensor

IGB3008BBPKG/AM/SC/V4A/US-104

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.6 / aluminium: 0.5 / copper: 0.2	
Hysteresis	[% of Sr]	3...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-40...85	
Protection		IP 65; IP 66; IP 67; IP 68; IP 69K	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
Impact resistance			1 J
Vibration resistance		EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance		EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance		EN 60068-2-27	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes
Fast temperature change		EN 60068-2-14 Na	TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles
MTTF	[years]	1176	
Embedded software included		yes	
UL approval		Ta	-25...70 °C
		Enclosure type	Type 1
		voltage supply	Limited Voltage/Current
		UL approval no.	A012
		File number UL	E174191
Mechanical data			
Weight	[g]	45	
Housing		threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M18 x 1 / L = 45	
Thread designation		M18 x 1	
Materials		stainless steel (316L/1.4404) anti-spatter; sensing face: stainless steel (316L/1.4404) anti-spatter; LED window: PEI; lock nuts: brass anti-spatter	
Tightening torque	[Nm]	20	
Full-metal housing		yes	
Displays / operating elements			
Display		switching status	4 x LED, yellow
		operation	1 x LED, green
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	


IGR207

Inductive full-metal sensor

IGB3008BBPKG/AM/SC/V4A/US-104

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 3, gold-plated



Connection

