


TA3317

Temperature transmitter

TA-050CLEN14-A-ZVG/US



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1	
Measuring range	0...100 °C	32...212 °F
Process connection	threaded connection 1/4" NPT external thread	
Installation length EL [mm]	50	

Application

Special feature	gold-plated contacts
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Pressure rating [bar]	400

Electrical data

Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog current output [mA]	4...20
Max. load [Ω]	(U _b - 8,5 V) / 21,5 mA; 24 V: 720 Ω
Short-circuit protection	yes
Overload protection	yes

Measuring/setting range

Probe length L [mm]	40.5
Measuring range	0...100 °C 32...212 °F

Resolution

Resolution of analog output [K]	0.04
---------------------------------	------

TA3317



Temperature transmitter

TA-050CLEN14-A-ZVG/US

Accuracy / deviations		
Precision analog output	[K]	$\pm 0,3 + (\pm 0,1 \% \text{ MS})$
Temperature coefficient	[% of the span / 10 K]	0,1; (In case of deviation from the reference condition $25 \pm 5 \text{ }^{\circ}\text{C}$)
Reaction times		
Dynamic response T05 / T09	[s]	1 / 3; (according to DIN EN 60751)
Operating conditions		
Ambient temperature	[$^{\circ}\text{C}$]	-40...100
Storage temperature	[$^{\circ}\text{C}$]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	1092
UL approval	UL approval number	K005
Mechanical data		
Weight	[g]	97.5
Housing		tubular
Dimensions	[mm]	$\varnothing 18.8 / L = 110.8$
Material		stainless steel (1.4404 / 316L); PEI; FKM
Materials (wetted parts)		stainless steel (1.4404 / 316L)
Process connection		threaded connection 1/4" NPT external thread
Probe diameter	[mm]	6
Installation length EL	[mm]	50
Remarks		
Remarks	The values for accuracy apply to flowing water. referring to UL: for use on a low voltage circuit with overcurrent protection in accordance with UL873 tab. 28.1 or $I_{\text{max}} = 100/U_b$ (U_b = voltage of the circuit)	
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: 2, gold-plated		
		


TA3317



Temperature transmitter

TA-050CLEN14-A-ZVG/US

Connection



OUT: analog output
Colors to DIN EN 60947-5-2