
AC5224

AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67



Application		
Design		housing for DIN rail mounting
Application		field installation
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i	[mA]	250
Max. current load total	[A]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	18...30
Max. total current rating of inputs	[mA]	200; (current load for all inputs and outputs: 200 mA)
Input current High	[mA]	6...10
Input current Low	[mA]	0...2
Switching level high	[V]	> 11
Digital inputs protected against short circuits		yes

AC5224

AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67

Outputs						
Number of digital outputs		2				
Circuit		PNP				
Voltage range DC	[V]	18...30				
Max. current load per output	[mA]	200; (current load for all inputs and outputs: 200 mA)				
Short-circuit proof		yes				
Electrically separated		no				
Actuator supply outputs		AS-i				
Operating conditions						
Ambient temperature	[°C]	-25...70				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
		IEC 61000-6-2				
MTTF	[years]	318				
AS-i classification						
AS-i version		2.11; 3.0				
AS-i addressing		addressing socket				
Extended addressing mode		yes				
AS-i master profile		M2; M3; M4				
AS-i profile		S-B.A.E				
AS-i I/O configuration	[hex]	B				
AS-i ID code	[hex]	A.E				
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	-	-	3	4
		socket	-	-	I-3/4	I-3/4 I-4
		pin	-	-	4	2 4
		Output	1	2	-	-
		socket	O-1/2	O-1/2 / O-2	-	-
		pin	4	2 4	-	-
Mechanical data						
Weight	[g]	155.95				
Housing		rectangular				
Type of mounting		quick mounting; AS-i flat cables directly connectable; mounting on DIN rail; (TH35 (EN 60715))				
Dimensions	[mm]	103 x 45 x 44.7				
Materials		PA; piercing contacts: CuSn6 nickel-plated and tin-plated				
Displays / operating elements						
Display		operation	LED, green			
		errors	LED, red			
		function	LED, yellow			
Electrical connection						
Module connection		Flat cables				
Accessories						
Items supplied		lower part				

AC5224

AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67

Accessories (optional)	Protective cap: M12, E73004

Remarks


Pack quantity	1 pcs.

Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Electrical connection - Inputs

Connection



Connector: M12

	Inputs
	socket I-3/4
1	Sensor supply L+
2	data input 4
3	Sensor supply L-
4	data input 3
5	not used
	socket I-4
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 4
5	not used


AC5224

AS-Interface ClassicLine module with quick mounting technology

ClassicL 2DO-Y 2DI-Y IP67

Electrical connection - Outputs

Connection



Connector: M12

	Outputs
	socket O-1/2
1	not used
2	switching output 2
3	Voltage L -
4	switching output 1
5	not used
	socket O-2
1	not used
2	not used
3	Voltage L -
4	switching output 2
5	not used