


CR2052



I/O modules for mobile machines

ioControl/In 8/Out 8/DT6



- 1+2 Programming buttons
- 3 Display
- 4 DEUTSCH connector
- 5 AMP connector



Electrical data

Operating voltage	[V]	8...32 DC
Reverse polarity protection		yes

Inputs / outputs

Total number of inputs and outputs	16
Number of inputs and outputs	Number of digital inputs: 8; Number of analog inputs: 4; Number of frequency inputs: 4; Number of resistor inputs: 4; Number of digital outputs: 8



I/O modules for mobile machines

ioControl/In 8/Out 8/DT6

Inputs		
Total number of inputs		8
Number of frequency inputs		4
Number of resistor inputs		4
Number of digital inputs		8
Number of analog inputs		4
Analog input (current)	[mA]	0...20
Analog input (voltage)	[V]	0...32
Outputs		
Total number of outputs		8
Number of digital outputs		8
Short-circuit protection		yes
Number of PWM outputs		8
Number of PWM-I outputs		8
Software / programming		
Parameter setting options		input/output functions
PLC function to IEC 61131-3		yes
Interfaces		
Number of CAN interfaces		2
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-4	
MTTF	[years]	88
Mechanical data		
Weight	[g]	136.5
Housing		rectangular
Type of mounting		Backplane mounting
Dimensions	[mm]	234.2 x 76 x 40.5
Material		PA reinforced glass-fiber
Displays / operating elements		
Display		10-segment LED display, red/green 4-digit
Remarks		
Pack quantity		1 pcs.
Electrical connection - CAN interface 1		
Connector: 2 x DEUTSCH connector		



I/O modules for mobile machines


ioControl/In 8/Out 8/DT6

CAN IN	
1	GND_CAN
2	CAN1_H
3	V_CAN
4	V_CAN
5	CAN1_L
6	GND_CAN

CAN OUT	
1	GND_CAN
2	CAN1_H
3	V_CAN
4	V_CAN
5	CAN1_L
6	GND_CAN

Electrical connection - inputs / outputs

Connector: 8 x DEUTSCH connector




Inputs Con. 1, 3, 5, 7	
1	GND1
2	Input
3	VBBS
4	VBBS
5	Input
6	GND1

Outputs Con. 2, 4, 6, 8	
1	GND2
2	Output
3	not used
4	not used
5	Output
6	GND2

Electrical connection - supply / CAN interface 2

Connector: 1 x AMP connector



X1	
1	GND1
2	CAN2_L
3	GND2
4	VBBs
5	CAN2_H
6	VBB2