
E20639

Fibre optic diffuse reflection sensor

FT-11-EPA-M4/F2X0,5/2M



Application		
Function principle		Diffuse reflection sensor
Application		Small bending radius
Detection zone		
Range with fibre optic amplifier type		OB50; OBF; OCF; OO50
OB50		
Range fibre optics	[mm]	20
OBF		
Range fibre optics	[mm]	25
OCF (High Power)		
Range fibre optics	[mm]	400
OO50		
Range fibre optics	[mm]	60
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	33
Version of sensing head		straight
Sensing head thread		M4

E20639

Fibre optic diffuse reflection sensor

FT-11-EPA-M4/F2X0,5/2M

Sensing head length	[mm]	23
Total length	[mm]	2000
Min. bending radius	[mm]	10
Fibre arrangement		
Core diameter	[mm]	2 x 0.5
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE
Accessories		
Items supplied		hexagon nuts: 2 x M4
		tooth lock washers: 2
		Adapter: 1 x OCF
Accessories (optional)		Cutter for fibre optics:, E20600
Remarks		
Pack quantity		1 pcs.