
OPU201

Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS



1 potentiometer sensitivity
2 output function switch

Product characteristics		
Type of light		red light
Electrical data		
Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 30
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660
Outputs		
Electrical design		PNP
Output function		light-on/dark-on mode; (selectable)
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	5000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Diameter of the smallest detectable object	[mm]	0.3
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9

OPU201

Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Profiles		Smart Sensor - SSP 0	Generic Profiled Sensor
		Function	Device identification
		Function	Multiple switching signal
		Function	Process data variable
		Function	Device diagnosis
		Function	Teach channel
SIO mode		yes	
Required master port type		A	
Min. process cycle time	[ms]	3.2	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	978

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 67

Tests / approvals

EMC		EN 60947-5-2	
MTTF	[years]	709	

Mechanical data

Weight	[g]	74
Dimensions	[mm]	40 x 10 x 50
Fork depth D	[mm]	25
Fork width W	[mm]	20
Materials		housing: diecast zinc black anodised; lens: glass

Displays / operating elements

Display		switching status	1 x LED, yellow

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M8; coding: A; Contacts: 3




OPU201

Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Connection



4	OUT / IO-Link

Other data

operating mode adjustable via IO-Link

	standard	High Resolution	Power	Speed
Resolution	0.3 mm	0.2 mm	1.0 mm	0.3 mm
Repeatability	0.02 mm	0.02 mm	0.02 mm	0.02 mm
Switching frequency	5000 Hz	1500 Hz	250 Hz	8000 Hz

Repeatability	3 σ