
EVF505

Connection cable

VDOGH040VAP00,5P04STAH040VAP



Application			
Special feature			Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Application			hygienic and wet areas in the food industry
Free from silicone			yes
Electrical data			
Operating voltage	[V]		< 250 AC / < 300 DC
Protection class			II
Max. current load total	[A]		4
Operating conditions			
Ambient temperature	[°C]		-25...100
Ambient temperature (moving)	[°C]		0...100
Storage temperature	[°C]		-25...55
Storage humidity	[%]		10...100
Other climatic conditions for storage according to stated class			1K22/ DIN 60721-3-1
Protection			IP 65; IP 67; IP 68; IP 69K
Mechanical data			
Weight	[g]		64.9
Dimensions	[mm]		35.5 x 15.5 x 38
Moulded-body material			PP, Halogen-free
Material nut			stainless steel (316L/1.4404)
Sealing material			EPDM
Drag chain suitability			yes
Drag chain suitability		bending radius for flexible use	min. 10 x cable diameter
		travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
		bending cycles	> 1 Mio.
		torsional strain	± 180 °/m
Remarks			
Pack quantity			1 pcs.

EVF505

Connection cable

VDOGH040VAP00,5P04STAH040VAP

Electrical connection - plug


Connector: 1 x M12, angled; coding: A; Contacts: 4, gold-plated; Moulded body: PP, Halogen-free; Locking: stainless steel (316L/1.4404); Tightening torque: 0.6...1.2 Nm



Electrical connection


Cable: 0.5 m, MPPE, Halogen-free, grey, Ø 6.2 mm; 4 x 1.00 mm² (32 x Ø 0.2 mm)

Connection




Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: PP, Halogen-free; Locking: stainless steel (316L/1.4404); Sealing: EPDM; Tightening torque: 0.6...1.5 Nm



Diagrams and graphs

characteristic line for derating



Derating Imax * 0.8 (DIN EN 60512-5-2)

T Ambient temperature [°C]

I Current [A]