
IGC250

Inductive full-metal sensor

IGK34,5-APKG/AM/US-104/K0



Product characteristics			
Electrical design		PNP	
Output function		normally closed	
Sensing range	[mm]	4.5	
Housing		threaded type	
Dimensions	[mm]	M18 x 1 / L = 70	
Application			
Special feature		Gold-plated contacts; Full-metal housing; Correction factor K = 0	
Application		Use in machine tools, coolants and lubricants; ferrous only; aluminium chip immune	
Pressure rating		100 bar	10 MPa
Note on pressure rating		sensing face	
Electrical data			
Operating voltage	[V]	10...30 DC	
Current consumption	[mA]	< 20	
Protection class		III	
Reverse polarity protection		yes	
Outputs			
Electrical design		PNP	
Output function		normally closed	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	100	
Switching frequency DC	[Hz]	100	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	4.5	
Operating distance	[mm]	0...3.64	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.5	

IGC250

Inductive full-metal sensor

IGK34,5-APKG/AM/US-104/K0

Hysteresis	[% of Sr]	1...20	
Correction factor K = 0		yes	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 68; ("Coolant")	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
Impact resistance		EN 60068-2-27 Ehc	1 J
MTTF	[years]	1258	
Embedded software included		yes	
UL approval		Ta	-25...70 °C
		Enclosure type	Type 1
		voltage supply	Limited Voltage/Current
		UL approval no.	A012
		File number UL	E174191
Mechanical data			
Weight	[g]	55.3	
Housing		threaded type	
Mounting		flush mountable	
Dimensions	[mm]	M18 x 1 / L = 70	
Thread designation		M18 x 1	
Materials		housing: stainless steel (316L/1.4404); sensing face: stainless steel (316L/1.4404); LED window: PEI; lock nuts: stainless steel (316L/1.4404)	
Tightening torque	[Nm]	50	
Full-metal housing		yes	
Displays / operating elements			
Display		switching status	4 x 90° LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			

Connector: 1 x M12; coding: A; Contacts: 3, gold-plated



IGC250

Inductive full-metal sensor

IGK34,5-APKG/AM/US-104/K0

Connection

