


Retro-reflective sensor

OLP-HPKG/US-100

Article no longer available - archive entry

Alternative articles: O5P500 + E21122

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 39
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Max. voltage drop of function check output	[V]	3.5
Permanent current rating of switching output DC	[mA]	200



Retro-reflective sensor

OLP-HPKG/US-100

Short-time current rating of switching output [mA]	200
Switching frequency DC [Hz]	50
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range [m]	< 8; (Prismatic reflector Ø 80 E20005)
Polarisation filter available	yes

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 66

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular
Dimensions [mm]	75 x 27 x 62
Materials	housing: PBT
Lens material	front pane: PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4



Connection

