
AC2316

AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T M12



1 sensor 1
2 sensor 2

Product characteristics		
Electrical design		AS-i
Sensing range	[mm]	4
Housing		rectangular
Dimensions	[mm]	55 x 60 x 35
Application		
Application		position sensor for valve actuators; actuator control
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 160
Outputs		
Electrical design		AS-i
Permanent current rating of switching output DC	[mA]	100

AC2316

AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T M12

Detection zone			
Sensing range	[mm]	4	
Operating conditions			
Ambient temperature	[°C]	-20...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 50295	
		EN 61000-6-2	
MTTF	[years]	310	
AS-i classification			
AS-i version		2.1	
Extended addressing mode		yes	
AS-i I/O configuration	[hex]	7	
AS-i ID code	[hex]	A.E	
AS-i certificate		75002	
Mechanical data			
Weight	[g]	179	
Housing		rectangular	
Mounting		non-flush mountable	
Dimensions	[mm]	55 x 60 x 35	
Materials		housing: PBT	
Displays / operating elements			
Display		switching status	2 x LED, yellow
Accessories			
Items supplied		Reinforcement bracket: 1 x (39,5 x 17,5 x 1 mm), E11310	
		socket head screws: 2 x (M5 x 35 mm)	
		washers: 2	
Remarks			
Pack quantity		1 pcs.	

Electrical connection

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4; Locking: stainless steel (303/1.4305)




AC2316

AS-Interface dual sensor for pneumatic valve actuators

DUAL SENSOR T5 2SI 1DO T M12

Connection




Electrical connection

1	AS-i +
3	AS-i -

Electrical connection - socket

Connector: 1 x M12; coding: A; Contacts: 2; Locking: stainless steel (303/1.4305)



Outputs

3	external voltage -
4	switching output 1 +