


SM8621



Magnetic-inductive flow meter

SMN11XGXFRKG/US-100



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1			
Measuring range	0.2...150 l/min	0.012...9 m³/h	3.6...2376 gph	0.06...39.6 gpm
Process connection	threaded connection 1" NPT Internal thread DN25			

Application

Special feature	gold-plated contacts			
Media	Conductive liquids; water; water-based media			
Note on media	conductivity: $\geq 20 \mu\text{S/cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)			
Medium temperature	-4...194			
Pressure rating	16 bar		1.6 MPa	

Electrical data

Operating voltage	18...30 DC; (to SELV/PELV)
-------------------	----------------------------



Magnetic-inductive flow meter

SMN11XGXFRKG/US-100

Current consumption	[mA]	< 80
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	5
Measuring principle		magnetic-inductive

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
------------------------------	---

Inputs

Inputs	counter reset
--------	---------------

Outputs

Total number of outputs	2
Output signal	switching signal; analog signal; pulse signal; IO-Link; frequency signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	100
Number of analog outputs	1
Analog current output [mA]	4...20; (scalable)
Max. load [Ω]	500
Pulse output	flow rate meter
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Measuring/setting range

Measuring range	0.2...150 l/min	0.012...9 m³/h	3.6...2376 gph	0.06...39.6 gpm
Display range	-180...180 l/min	-10.8...10.8 m³/h	-2853.6...2853.6 gph	-47.56...47.56 gpm
Resolution	0.1 l/min	0.006 m³/h	0.6 gph	0.01 gpm
Set point SP	1...150 l/min	0.06...9 m³/h	16.2...2376 gph	0.27...39.6 gpm
Reset point rP	0.2...149.2 l/min	0.012...8.95 m³/h	3.6...1903 gph	0.06...39.42 gpm
Analog start point ASP	0...120 l/min	0...7.2 m³/h	0...1903 gph	0...31.71 gpm
Analog end point AEP	30...150 l/min	1.8...9 m³/h	475...2376 gph	7.92...39.6 gpm
Low flow cut-off LFC	0.2...7.5 l/min	0.012...0.45 m³/h	3...118.4 gph	0.05...1.98 gpm
Frequency end point, FEP	30.2...150 l/min	1.8...9 m³/h	480...2376 gph	8...39.6 gpm
Frequency at the end point FRP	[Hz]	1...10000		

Volumetric flow quantity monitoring

Pulse length	[s]	0.002...2
Pulse value		0.01...99990000 l

Temperature monitoring

Measuring range	[°F]	-4...194
Display range	[°F]	-43.6...233.6
Resolution	[°F]	0.1



Magnetic-inductive flow meter

SMN11XGXFRKG/US-100

Set point SP	[°F]	-3.3...194
Reset point rP	[°F]	-4...193.3
Analog start point	[°F]	-4...154.4
Analog end point	[°F]	35.6...194
In steps of	[°F]	0.1

Accuracy / deviations

Flow monitoring		
Accuracy (in the measuring range)		$\pm (0,8 \% MW + 0,2 \% MEW)$
Repeatability		$\pm 0,2 \% MEW$

Temperature monitoring

Accuracy	[K]	$\pm 2,5 (Q > 5 \% MEW)$
----------	-----	--------------------------

Reaction times

Flow monitoring		
Start-up delay	[s]	0...50
Response time	[s]	$< 0.25; (dAP = 0, T09)$
Damping process value dAP	[s]	0...5

Temperature monitoring

Response time	[s]	15; $(Q > 10 \% MEW, T09)$
---------------	-----	----------------------------

Software / programming

Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/pulse output; Start-up delay; display can be deactivated; Display unit; Frequency output	
---------------------------	--	--

Interfaces

Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Common - I&D	Identification and Diagnosis
	Function	Measurement data, standard resolution
SIO mode	yes	
Required master port class	A	
Process data analog	3	
Process data binary	2	
Min. process cycle time	[ms]	8
Supported DeviceIDs	Type of operation	DeviceID
	default	964

Operating conditions

Ambient temperature	[°F]	-4...140
Storage temperature	[°F]	-13...176
Protection	IP 65; IP 67	

Tests / approvals

EMC	DIN EN 60947-5-9	
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6:	5 g (10...2000 Hz)

SM8621



Magnetic-inductive flow meter

SMN11XGXFRKG/US-100

MTTF	[years]	114
UL approval	UL approval number	I014
	File number UL	E174189
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight	[g]	777
Housing		rectangular
Dimensions	[mm]	110 x 48 x 73
Material		stainless steel (1.4408/316); stainless steel (1.4404 / 316L); PC; PBT+PC-GF30
Materials (wetted parts)		stainless steel (1.4404 / 316L); PEEK; carbon fiber PEEK; FKM
Process connection		threaded connection 1" NPT Internal thread DN25

Displays / operating elements

Display	Color display 1,44", 128 x 128 pixels
	2 x LED, yellow

Remarks

Remarks	MW = Measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



SM8621



Magnetic-inductive flow meter

SMN11XGXFRKG/US-100

Connection



OUT1:	Colors to DIN EN 60947-5-2
	Switching output Volumetric flow quantity monitoring
	Switching output Temperature monitoring
	Pulse output quantity meter
	Frequency output volumetric flow monitoring
	Frequency output Temperature monitoring
	signal output Preset counter
OUT2:	IO-Link
	Switching output Volumetric flow quantity monitoring
	Switching output Temperature monitoring
	analog output flow
	analog output temperature
	Input counter reset
	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white


SM8621

Magnetic-inductive flow meter

SMN11XGXFRKG/US-100



Diagrams and graphs



Pressure loss / volumetric flow quantity