




Programmable controller for mobile machines

R360/CabinetController/16B



Electrical data		
Operating voltage	[V]	10...32 DC
Inputs / outputs		
Total number of inputs and outputs		42
Number of inputs and outputs		Number of digital inputs: 24; Number of analogue inputs: 8; Number of frequency inputs: 4; Number of digital outputs: 18
Inputs		
Number of frequency inputs		4
Number of digital inputs		24
Number of analogue inputs		8
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	0...32
Outputs		
Number of digital outputs		18



Programmable controller for mobile machines

R360/CabinetController/16B

Number of PWM outputs	8
Number of high-current outputs	6
Software / programming	
Parameter setting options	input/output functions
PLC function to IEC 61131-3	yes
Interfaces	
Number of CAN interfaces	2
Number of R232 interfaces	1
Tests / approvals	
MTTF [years]	73
Mechanical data	
Weight [g]	136.5
Housing	rectangular
Type of mounting	backplane mounting
Dimensions [mm]	226 x 133 x 39
Remarks	
Pack quantity	1 pcs.