
O8E201

Through-beam sensor receiver

O8E-DNKG/2,0M



receiver in upper lens

Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Function principle		Through-beam sensor
Application		For applications in robotics, assembly and handling technology
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	15; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Outputs		
Electrical design		NPN
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000

O8E201

Through-beam sensor receiver

O8E-DNKG/2,0M

Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Detection zone			
Transmitter / receiver		receiver	
Range	[m]	< 3	
Operating conditions			
Ambient temperature	[°C]	-25...60	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]	1152	
UL approval		Ta	-25...60 °C
		Enclosure type	Type 1
		voltage supply	Limited Voltage/Current
		UL approval no.	E014
		File number UL	E174191
Mechanical data			
Weight	[g]	38	
Housing		rectangular	
Dimensions	[mm]	28.1 x 8.1 x 14.4	
Materials		housing: ABS; rear of the housing: stainless steel (316L/1.4404)	
Lens material		front pane:PMMA	
Lens alignment		side lens	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	

O8E201


Through-beam sensor receiver

O8E-DNKG/2,0M

Electrical connection

Cable: 2 m, PVC, black, Ø 2.9 mm; 3 x 0.08 mm²


Connection



	Core colours :
BN =	brown
BK =	black
BU =	blue

Diagrams and graphs

excess gain graph



x: distance [mm]

y: excess gain factor