


SM9000



Magnetic-inductive flow meter

SMR21XGXFRKG/US



CE PA CRN cUL US LISTED EC 1935/2004 FCM JP IO-Link UK CA

Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Measuring range	5...300 l/min	0.3...18 m³/h
Process connection	threaded connection G 2 external thread DN50 flat seal	

Application

Special feature	gold-plated contacts
Application	Totalizer function; empty pipe detection; for industrial applications
Installation	connection to pipe by means of an adapter
Media	Conductive liquids; water; water-based media

SM9000



Magnetic-inductive flow meter

SMR21XGXFRKG/US

Note on media	conductivity: $\geq 20 \mu\text{S/cm}$	
	viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)	
Medium temperature [°C]	-10...90	
Pressure rating	16 bar	1.6 MPa
MAWP (for applications according to CRN)	8.9 bar	0.89 MPa

Electrical data		
Operating voltage [V]	18...32 DC; (to SELV/PELV)	
Current consumption [mA]	< 150	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time [s]	5	
Measuring principle	magnetic-inductive	

Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1

Inputs	
Inputs	counter reset

Outputs		
Total number of outputs	2	
Output signal	switching signal; analog signal; pulse signal; frequency signal; IO-Link; (configurable)	
Electrical design	PNP/NPN	
Number of digital outputs	2	
Output function	normally open / closed; (configurable)	
Max. voltage drop switching output DC [V]	2	
Permanent current rating of switching output DC [mA]	250; (per output)	
Number of analog outputs	1	
Analog current output [mA]	4...20; (scalable)	
Max. load [Ω]	500	
Analog voltage output [V]	0...10; (scalable)	
Min. load resistance [Ω]	2000	
Pulse output	flow rate meter	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Frequency of the output [Hz]	0.1...10000	

Measuring/setting range		
Measuring range	5...300 l/min	0.3...18 m³/h
Display range	-360...360 l/min	-21.6...21.6 m³/h
Resolution	0.5 l/min	0.02 m³/h
Set point SP	6.5...300 l/min	0.4...18 m³/h
Reset point rP	5...298.5 l/min	0.3...17.9 m³/h
Analog start point ASP	0...240 l/min	0...14.4 m³/h
Analog end point AEP	60...300 l/min	3.6...18 m³/h

SM9000



Magnetic-inductive flow meter

SMR21XGXFRKG/US

Low flow cut-off LFC	< 15 l/min		< 0.9 m³/h
In steps of	0.5 l/min		0.02 m³/h
Measuring dynamics	1:60		
Volumetric flow quantity monitoring			
Pulse value	0.0001...300 x 10³ m³		
In steps of	0.0001 m³		
Pulse length [s]	0,016...2		
Temperature monitoring			
Measuring range [°C]	-20...80		
Display range [°C]	-40...100		
Resolution [°C]	0.2		
Set point SP [°C]	-19.2...80		
Reset point rP [°C]	-19.6...79.6		
Analog start point [°C]	-20...60		
Analog end point [°C]	0...80		
In steps of [°C]	0.2		
Accuracy / deviations			
Flow monitoring			
Accuracy (in the measuring range)	± (0,8 % MW + 0,5 % MEW)		
Repeatability	± 0,2% MEW		
Temperature monitoring			
Temperature drift	± 0,0333 °C / K		
Accuracy [K]	± 1 (25 °C; Q > 15 l/min)		
Reaction times			
Flow monitoring			
Response time [s]	0.35; (dAP = 0)		
Delay time programmable dS, dr [s]	0...50		
Damping process value dAP [s]	0...5		
Temperature monitoring			
Dynamic response T05 / T09 [s]	T09 = 3 (Q > 15 l/min)		
Software / programming			
Parameter setting options	Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / closed; switching logic; current/voltage/frequency/pulse output; Start-up delay; display can be deactivated; Display unit; empty pipe detection		
Interfaces			
Communication interface	IO-Link		
Transmission type	COM2 (38,4 kBaud)		
IO-Link revision	1.1		
SDCI standard	IEC 61131-9 CDV		
Profiles	Smart Sensor - SSP 0	Generic Profiled Sensor	
	Function	Device identification	
	Function	Process data variable	

SM9000



Magnetic-inductive flow meter

SMR21XGXFRKG/US

SIO mode	yes	
Required master port class	A	
Process data analog	3	
Process data binary	2	
Min. process cycle time [ms]	5	
Supported DeviceIDs	Type of operation	DeviceID
	default	391

Operating conditions		
Ambient temperature [°C]		-10...60
Storage temperature [°C]		-25...80
Protection		IP 65; IP 67

Tests / approvals		
EMC	DIN EN 60947-5-9	
CPA approval	model number	004MI
	accuracy class	-
	maximum allowable error	± 1,5 % FS
	Q (min)	0,3 m³/h
	Q (t)	-
	Q (max)	18 m³/h
	Medium temperature	-10...70°C
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]		85
UL approval	UL approval number	I008
	File number UL	E174189
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		3176
Housing		rectangular
Inlet pipe length		3 x DN
Outlet pipe length		1 x DN
Dimensions [mm]		200 x 103 x 117
Material	stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); PEI; FKM; PBT-GF20; TPE-U	
Materials (wetted parts)	Pipe section: stainless steel (1.4404 / 316L); Process connection sealing: NBR fiber-reinforced Gasket; FKM; stainless steel (1.4571/316Ti); PEEK	
Process connection	threaded connection G 2 external thread DN50 flat seal	

Displays / operating elements		
Display	Display unit	6 x LED, green (l/min, m³/h, l, m³, 10³, °C)
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit

Accessories		
Items supplied	sealings: 2, Centellen	
	Label	

SM9000



Magnetic-inductive flow meter

SMR21XGXFRKG/US


Remarks	
Remarks	MW = Measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



- OUT1:	Colors to DIN EN 60947-5-2 Switching output empty pipe detection Switching output Volumetric flow quantity monitoring Frequency output Volumetric flow quantity monitoring Pulse output quantity meter signal output Preset counter IO-Link
OUT2:	Switching output empty pipe detection Switching output Volumetric flow quantity monitoring Switching output Temperature monitoring analog output Volumetric flow quantity monitoring analog output Temperature monitoring Input counter reset Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white

SM9000




Magnetic-inductive flow meter

SMR21XGXFRKG/US

Diagrams and graphs

Pressure loss



dP Pressure loss
Q volumetric flow quantity