
ID5059

Inductive sensor

IDC4050UCPKG/SC/2LED/US-100DPA



1 mounting on DIN rail

Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	50
Housing		rectangular
Dimensions	[mm]	92 x 80 x 40
Application		
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	70
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

ID5059


Inductive sensor

IDC4050UCPKG/SC/2LED/US-100DPA

Detection zone			
Sensing range	[mm]	50	
Operating distance	[mm]	0...40.5; (mounted flush with mild steel (ST37))	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.85 / brass: 0.48 / aluminium: 0.46 / copper: 0.38	
Hysteresis	[% of Sr]	3...20	
Switch point drift	[% of Sr]	-15...15	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]	1162	
UL approval		Ta	-25...70 °C
		Enclosure type	Type 1
		voltage supply	Class 2
		File number UL	E174191
Mechanical data			
Weight	[g]	422.5	
Housing		rectangular	
Mounting		flush mountable	
Type of mounting		mounting on DIN rail; (TH35 (EN 60715))	
Dimensions	[mm]	92 x 80 x 40	
Materials		PPE anti-spatter; brass white bronze coated; diecast zinc	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Accessories			
Items supplied		sealing plug: 1	
Remarks			
Pack quantity		1 pcs.	

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4



ID5059

Inductive sensor

IDC4050UCPKG/SC/2LED/US-100DPA

Connection

