
OGS701

Through-beam laser sensor transmitter

OGSLOOKG/US100



Product characteristics		
Type of light		red light
Laser protection class		1
Housing		threaded type
Application		
Function principle		Through-beam sensor
Application		Industrial applications / factory automation
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	13
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	655
Typ. lifetime	[h]	50000
Detection zone		
Transmitter / receiver		transmitter
Range	[m]	< 2
Range adjustable		no
Diameter of the smallest detectable object	[mm]	0.5; (2 m)
Max. light spot diameter	[mm]	5
Light spot dimensions refer to		at maximum range
Operating conditions		
Ambient temperature	[°C]	-10...60
Protection		IP 65; IP 67
Tests / approvals		
EMC		EN 60947-5-2
Laser protection class		1

OGS701

Through-beam laser sensor transmitter

OGSLOOKG/US100

Notes on laser protection		Caution:	laser light
		laser class:	1
			EN / IEC60825-1:2007
			EN / IEC60825-1:2014
			Complies with 21 CFR 1040.10 except for conformance with IEC 60825-1 Ed. 3, as described in Laser Notice No. 56, dated May 8, 2019.
MTTF	[years]	1018	

Mechanical data

Weight	[g]	64
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 72
Thread designation		M18 x 1
Materials		stainless steel (316L/1.4404); PA; EPDM
Lens material		front pane:PMMA

Displays / operating elements

Display	operation	1 x LED, green

Accessories

Items supplied	lock nuts: 2

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4



Connection

