


TT3050



Temperature probe sensor

TT-300KBBD10-...../US/



- 1 plug area
L = Probe length corresponds to installation length EL



Product characteristics

Measuring range	-40...150 °C	-40...302 °F
Process connection	Clamp fitting Ø 10 mm	
Installation length EL [mm]	360	

Application

Special feature	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating	160 bar	16 MPa
Minimum installation depth [mm]	15	

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	360	
Measuring range		-40...150 °C	-40...302 °F

Accuracy / deviations

Accuracy [K]	± (0,15 K + 0,002 x t)
--------------	-------------------------

Reaction times

Dynamic response T05 / T09 [s]	1 / 3; (according to DIN EN 60751)
--------------------------------	------------------------------------

Operating conditions

Ambient temperature [°C]	-25...80
Note on ambient temperature	plug area
Storage temperature [°C]	-40...100
Protection	IP 68; IP 69K

Tests / approvals

Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]	22831	

Mechanical data

Weight [g]	100.3
Housing	tubular
Dimensions [mm]	Ø 10 / L = 381.5

TT3050



Temperature probe sensor

TT-300KBBD10-...../US/

Material	stainless steel (1.4404 / 316L)
Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	Clamp fitting Ø 10 mm
Probe diameter [mm]	10
Installation length EL [mm]	360

Remarks	
Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

