
ROP521

Incremental encoder with hollow shaft and display

INCREMENTAL ENCODER PERFORMANCE LINE



1 M3
2 display

Product characteristics		
Resolution		1...10000; (parameterisable; Factory setting: 1024) resolution
Communication interface		IO-Link
Shaft design		hollow shaft open to one side
Shaft diameter	[mm]	12
Application		
Function principle		incremental
Detection system		magnetic
Application		encoder; Speed monitor; counter
Electrical data		
Operating voltage	[V]	4.75...30 DC
Current consumption	[mA]	< 350
Protection class		III
Reverse polarity protection		yes
Max. revolution electrical	[U/min]	12000
Outputs		
Electrical design		HTL/TTL
Switching frequency	[kHz]	1000
Factory setting		Output function: HTL (50 mA)
Short-circuit protection		yes
Phase difference A and B	[°]	90
Measuring/setting range		
Resolution		1...10000; (parameterisable; Factory setting: 1024) resolution

ROP521

Incremental encoder with hollow shaft and display

INCREMENTAL ENCODER PERFORMANCE LINE

Speed monitor			
Set point SP		-9994...9999 U/min	-166.6...166.7 Hz
Reset point rP		-9999...9994 U/min	-166.7...166.6 Hz
Counter			
Preset point		1...9999	
Accuracy / deviations			
Accuracy	[°]	0.1	
Software / programming			
Parameter setting options		encoder; Resolution; direction of rotation; HTL; TTL; Speed monitor; Resolution	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
Profiles		Smart Sensor - SSP 0	Generic Profiled Sensor
		Function	Device identification
		Function	Process data variable
		Function	Device diagnosis
SIO mode		yes	
Min. process cycle time	[ms]	2.7	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	496
Operating conditions			
Ambient temperature	[°C]	-40...85	
Storage temperature	[°C]	-40...85	
Max. relative air humidity	[%]	95; (condensation not permissible)	
Protection		IP 65; (on the housing: IP 67; on the shaft: IP 65)	
Tests / approvals			
Shock resistance			100 g
Vibration resistance			20 g
MTTF	[years]	218	
Mechanical data			
Weight	[g]	481.5	
Housing		cylindrical	
Dimensions	[mm]	Ø 58 / L = 56.2	
Materials		flange: aluminium; housing: stainless steel (444/1.4521); display window: PEI	
Max. revolution, mechanical	[U/min]	12000	
Max. starting torque	[Nm]	0.02	
Reference temperature torque	[°C]	20	
Shaft design		hollow shaft open to one side	
Shaft diameter	[mm]	12	
Shaft material		stainless steel	
Installation depth of shaft	[mm]	27	
Max. axial shaft misalignment	[mm]	0,5	


ROP521

Incremental encoder with hollow shaft and display

INCREMENTAL ENCODER PERFORMANCE LINE

Fixing flange	Ø 58 mm	
Displays / operating elements		
Display		10-segment display, red/green 4-digit parameterisable
		2 x LED, yellow
		5 x LED, green
Accessories		
Items supplied	Stator coupling: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12, radial, can also be used axially; coding: A; Contacts: 8; Moulded body: stainless steel (316 / 1.4401); Maximum cable length: 100 m; (IO-Link: max. 20 m)



IO-Link	
1	L+
2	not to be used
3	L-
4	IO-Link
5	not to be used
6	not to be used
7	not to be used
8	not to be used
Screen	plug

encoder	
1	UB
2	A
3	GND
4	Z/0-Pulse (90 deg)
5	B
6	A-
7	B-
8	Z-
Screen	plug

Preset counter	
1	UB
2	IN1
3	GND
4	not to be used
5	OUT1
6	not to be used
7	not to be used
8	not to be used
Screen	plug

ROP521


Incremental encoder with hollow shaft and display

INCREMENTAL ENCODER PERFORMANCE LINE

Speed monitor	
1	UB
2	OUT2
3	GND
4	not to be used
5	OUT1
6	OUT2-
7	OUT1-
8	not to be used
Screen	plug

Diagrams and graphs

Pulse diagram



direction of rotation clockwise (looking at the shaft)