


SU6621

Ultrasonic flow meter

SUN12XXBFRKG/US



KTW/W270



Reg31

Product characteristics

Measuring range	0.5...65 l/min	0.03...3.9 m³/h	8...1030 gph	0.13...17.17 gpm
Process connection	threaded connection 1/2" NPT external thread DN15			

Application

Special feature	gold-plated contacts	
Media	ultra-pure water; water; water-based media	
Note on media	water-based media: for media with >10 % additives, the repeatability is the only available value	
Medium temperature	-20...100 °C	-4...212 °F
Min. burst pressure	150 bar	15 MPa
Pressure rating	100 bar	10 MPa
Vacuum resistance [mbar]	-1000	

Electrical data

Operating voltage [V]	18...32 DC; (to SELV/PELV)		
Current consumption [mA]	< 75		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	5		
Measuring principle	ultrasonic		

Inputs

Inputs	counter reset
--------	---------------

Outputs

Total number of outputs	2
-------------------------	---

SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US

Output signal	switching signal; pulse signal; analog signal; IO-Link; frequency signal; diagnostic signal; totalizer switching signal	
Electrical design	PNP/NPN	
Output function	normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	0...10000
Analog current output	[mA]	4...20
Max. load	[Ω]	500
Pulse output	flow rate meter	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	

Measuring/setting range				
Measuring range	0.5...65 l/min	0.03...3.9 m³/h	8...1030 gph	0.13...17.17 gpm
Display range	-78...78 l/min	-4.68...4.68 m³/h	-1236...1236 gph	-20.61...20.61 gpm
Resolution	0.1 l/min	0.002 m³/h	1 gph	0.01 gpm
Set point SP	0.9...65 l/min	0.052...3.9 m³/h	14...1030 gph	0.23...17.17 gpm
Reset point rP	0.5...64.7 l/min	0.032...3.88 m³/h	8...1025 gph	0.14...17.08 gpm
Analog start point ASP	-65...52 l/min	-3.9...3.12 m³/h	-1030...824 gph	-17.17...13.74 gpm
Analog end point AEP	-52...65 l/min	-3.12...3.9 m³/h	-824...1030 gph	-13.74...17.17 gpm
Low flow cut-off LFC	0.5...3.2 l/min	0.03...0.195 m³/h	8...52 gph	0.13...0.86 gpm
Frequency end point, FEP	13...65 l/min	0.782...3.9 m³/h	207...1030 gph	3.44...17.17 gpm
Frequency at the end point FRP	[Hz]	1...10000		

Volumetric flow quantity monitoring	
Pulse length	[s] 0.002...2
Pulse value	0.02...99990000 l; 0.005...26414563.515 gal

Temperature monitoring		
Measuring range	-20...100 °C	-4...212 °F
Display range	-44...124 °C	-47.2...255.2 °F
Resolution	0.1 °C	0.1 °F
Set point SP	-19.6...100 °C	-3.2...212 °F
Reset point rP	-20...99.6 °C	-4...211.2 °F
Analog start point	-20...76 °C	-4...168.8 °F
Analog end point	4...100 °C	39.2...212 °F
Frequency start point, FSP	-20...76 °C	4...168.8 °F
Frequency end point, FEP	4...100 °C	4...212 °F
Frequency at the end point FRP	[Hz]	1...10000

Accuracy / deviations	
Flow monitoring	
Accuracy (in the measuring range)	± (2,0 % MW + 0,5 % MEW)
Repeatability	± 0,2 % MEW



Ultrasonic flow meter

SUN12XXBFRKG/US

Temperature monitoring		
Accuracy	[K]	$\pm 2,5$ (Q > 5 % MEW)
Temperature coefficient		0,2
	[% of the span / 10 K]	
Reaction times		
Flow monitoring		
Response time	[s]	< 0.25; (dAP = 0, T09)
Damping process value dAP	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	5,7 / 86
Software / programming		
Diagnostic functions		direction of flow detection; signal quality
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9: 2013-07
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
Required master port class		A
Process data analog		3
Process data binary		2
Min. process cycle time	[ms]	9.6
IO-Link process data (cyclical)	Function	bit length
	totalizer	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1462
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN 61326-1:2021	
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF	[years]	160
UL approval	UL approval number	I034
Pressure equipment directive		can be used for group 2 fluids; group 1 fluids on request

SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US

Mechanical data		
Weight	[g]	524.7
Housing		rectangular
Type of mounting		inlet pipe length 5xDN; outlet pipe length 1xDN
Dimensions	[mm]	148 x 48 x 55.2
Material		housing: stainless steel (1.4404 / 316L); Display: PFA; sealing Display: FKM; connector: PBT
Materials (wetted parts)		Pipe section: stainless steel (1.4404 / 316L)
Process connection		threaded connection 1/2" NPT external thread DN15
Surface characteristics Ra/Rz of the wetted parts		49.21 µin
Displays / operating elements		
Display		Color display 1,44", 128 x 128 pixels
	Switching function	2 x LED, yellow
	diagnosis	1 x LED, three-color
Accessories		
Items supplied		package insert
Remarks		
Remarks		MW = Measured value
		MEW = Final value of the measuring range
		pulse and totalizer signal are only available for one of the two outputs
		the accuracy indications are adhered to over the entire application area
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: 4, gold-plated		


SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US

Connection



- OUT1/IO-Link:
- Switching output Volumetric flow quantity monitoring
 - Switching output Temperature monitoring
 - Pulse output quantity meter
 - Frequency output Volumetric flow quantity monitoring
 - Frequency output Temperature monitoring
 - Diagnostic output direction of flow detection / signal quality
 - signal output Preset counter
- OUT2/InD:
- Switching output Volumetric flow quantity monitoring
 - Switching output Temperature monitoring
 - Pulse output quantity meter
 - analog output flow
 - analog output temperature
 - Diagnostic output direction of flow detection / signal quality
 - signal output Preset counter
 - Input counter reset

Colors to DIN EN 60947-5-2

- Core colors
- BK= black
 - BN= brown
 - BU= blue
 - WH= white

SU6621


Ultrasonic flow meter

SUN12XXBFRKG/US




Diagrams and graphs

Note on pressure loss



derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature