


SUH201

Ultrasonic flow meter

SUC251JBFRKG/US



Reg31

Product characteristics				
Measuring range	1...240 l/min	0.06...14.4 m³/h	16...3804 gph	0.26...63.4 gpm
Nominal diameter	DN25 (1“)			
Process connection	Clamp 1" DIN 32676 series C (ASME BPE)			
Application				
Special feature	gold-plated contacts			
Media	ultra-pure water; water; water-based media; edible oils			
Note on media	water-based media: for media with >10 % additives, the repeatability is the only available value			
	edible oils: palm oil, soy oil, rapeseed oil, sunflower oil, peanut oil, olive oil and others			
Medium temperature	-20...100 °C		-4...212 °F	
Min. burst pressure	75 bar		7.5 MPa	
Pressure rating	25 bar		2.5 MPa	
Note on pressure rating	take into account the pressure resistance of the bracket and the seal used for clamp connection			
Vacuum resistance	[mbar]	-1000		
Electrical data				
Operating voltage	[V]	18...32 DC; (to SELV/PELV)		
Current consumption	[mA]	< 75		
Protection class		III		



Ultrasonic flow meter

SUC251JBFRKG/US

Reverse polarity protection	yes			
Power-on delay time [s]	5			
Measuring principle	ultrasonic			
Inputs / outputs				
Total number of inputs and outputs	2			
Inputs				
Inputs	OUT2		counter reset	
Outputs				
Total number of outputs	2			
Output signal	OUT1		switching signal; pulse signal; diagnostic signal; totalizer switching signal; frequency signal; IO-Link	
	OUT2		switching signal; pulse signal; diagnostic signal; totalizer switching signal; analog signal	
Electrical design	PNP/NPN			
Min. load resistance [Ω]	2000			
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	yes (non-latching)			
Overload protection	yes			
Analog				
Number of analog outputs	1			
Analog current output [mA]	4...20			
Max. load [Ω]	500			
Digital				
Number of digital outputs	2			
Output function	normally open / closed; (configurable)			
Max. voltage drop switching output DC [V]	2			
Permanent current rating of switching output DC [mA]	100			
Switching frequency DC [Hz]	0...10000			
Measuring/setting range				
Measuring range	1...240 l/min	0.06...14.4 m³/h	16...3804 gph	0.26...63.4 gpm
Display range	-288...288 l/min	-17.28...17.28 m³/h	-4565...4565 gph	-76.08...76.08 gpm
Resolution	0.1 l/min	0.001 m³/h	1 gph	0.02 gpm
Set point SP	2.3...240 l/min	0.139...14.4 m³/h	37...3804 gph	0.61...63.4 gpm
Reset point rP	1.1...238.8 l/min	0.064...14.325 m³/h	17...3784 gph	0.28...63.07 gpm
Analog start point ASP	-240...192 l/min	-14.4...11.522 m³/h	-3804...3044 gph	-63.4...50.73 gpm
Analog end point AEP	-191.9...240 l/min	-11.511...14.4 m³/h	-3041...3804 gph	-50.68...63.4 gpm
Low flow cut-off LFC	1...12 l/min	0.06...0.72 m³/h	16...190 gph	0.26...3.17 gpm
Frequency end point, FEP	48.1...240 l/min	2.889...14.4 m³/h	763...3804 gph	12.72...63.4 gpm
Frequency at the end point FRP [Hz]	1...10000			



Ultrasonic flow meter

SUC251JBFRKG/US

Volumetric flow quantity monitoring		
Pulse length	[s]	0.002...2
Pulse value		0.02...99990000 l; 0.0053...26414563.515 gal
Temperature monitoring		
Measuring range	-20...100 °C	-4...212 °F
Display range	-44...124 °C	-47.2...255.2 °F
Resolution	0.1 °C	0.1 °F
Set point SP	-19.6...100 °C	-3.2...212 °F
Reset point rP	-20...99.6 °C	-4...211.2 °F
Analog start point	-20...76 °C	-4...168.8 °F
Analog end point	4...100 °C	39.2...212 °F
Frequency start point, FSP	-20...76 °C	-4...168.8 °F
Frequency end point, FEP	4...100 °C	39.2...212 °F
Frequency at the end point FRP	[Hz]	1...10000
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)	edible oils	± (5,0 % MW + 1,0 % MEW)
	water	± (1,0 % MW + 0,5 % MEW)
Repeatability	± 0,2 % MEW	
Temperature monitoring		
Accuracy	[K]	± 2,5 (Q > 5 % MEW)
Temperature coefficient [% of the span / 10 K]	0,2	
Reaction times		
Flow monitoring		
Response time	[s]	< 0.25; (dAP = 0, T09)
Damping process value dAP	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	5,7 / 86
Software / programming		
Diagnostic functions	direction of flow detection; signal quality	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9: 2013-07	
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
Required master port class	A	
Process data analog	3	
Process data binary	2	
Min. process cycle time	[ms]	9.6



Ultrasonic flow meter

SUC251JBFRKG/US

IO-Link process data (cyclical)	Function	bit length
	totalizer	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
Supported DeviceIDs	Output 2	1
	Type of operation	DeviceID
	default	1751

Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 69K

Tests / approvals		
EMC	DIN 61326-1:2021	
CPA approval	model number	003US
	accuracy class	1,5
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF	[years]	160
UL approval	UL approval number	I034
	File number UL	E174189
Pressure equipment directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	639.4
Housing		rectangular
Inlet pipe length		5 x DN
Outlet pipe length		1 x DN
Dimensions	[mm]	175 x 50.4 x 73.8
Material		housing: stainless steel (1.4404 / 316L); Display: PFA; sealing Display: FKM; connector: PBT
Materials (wetted parts)		Pipe section: stainless steel (1.4404 / 316L)
Nominal diameter		DN25 (1")
Process connection		Clamp 1" DIN 32676 series C (ASME BPE)
Process connection suitable for pipe standard		1" / Ø 25,4 mm x 1,65 mm (DIN 11866 series C); (DIN EN 10357 Series D)
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.8 µm (32 µin)

Displays / operating elements		
Display		Color display 1,44", 128 x 128 pixels
	Switching function	2 x LED, yellow
	diagnosis	1 x LED, three-color

Remarks	
Remarks	MW = Measured value
	MEW = Final value of the measuring range
	pulse and totalizer signal are only available for one of the two outputs
	the accuracy indications are adhered to over the entire application area

SUH201



Ultrasonic flow meter

SUC251JBFRKG/US


Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection




1 (L+)	L+	
2 (OUT2)	MP2	DO2, AO, DI
3 (L-)	L-	
4 (OUT1)	MP1	DO1, FO, IO-Link

AO: analog output; DI: digital input; DO: digital output; FO: Frequency output; MP: multi-function connection

Diagrams and graphs

Note on pressure loss



dP Pressure loss
[psi]
Q volumetric flow quantity
[gpm]


SUH201

Ultrasonic flow meter

SUC25IJBFRKG/US



derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature