


OU5034



Diffuse reflection sensor

OUT-HPKG/US-100-DPS



Product characteristics	
Type of light	Infrared light
Housing	rectangular
Application	
Function principle	Diffuse reflection sensor
Application	Industrial applications
Electrical data	
Operating voltage [V]	10...55 DC; (cULus - Class 2 source required)
Current consumption [mA]	35; ((24 V))
Protection class	III
Reverse polarity protection	yes
Type of light	Infrared light
Wave length [nm]	880
Outputs	
Electrical design	PNP
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	160
Short-circuit protection	yes
Overload protection	yes
Monitoring range	
Range [mm]	1...200; (white paper 200 x 200 mm)
Range adjustable	yes
Max. light spot diameter [mm]	180
Light spot dimensions refer to	at maximum range
Operating conditions	
Ambient temperature [°C]	-25...80

OU5034



Diffuse reflection sensor

OUT-HPKG/US-100-DPS

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
MTTF [years]	685	
UL approval	Ta	< 40 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	UL approval number	E032
	File number UL	E174191

Mechanical data

Weight [g]	73.4
Housing	rectangular
Dimensions [mm]	28 x 16 x 51
Number of channels	1
Material	housing: PPO modified
Lens material	front lens:glass

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories


Items supplied	Angle bracket: 1, E20211
----------------	--------------------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4



Connection





Diffuse reflection sensor

OUT-HPKG/US-100-DPS

Diagrams and graphs

excess gain graph

