


O7H200



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS



Receiver in upper lens
transmitter in lower lens



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		Background suppression
Function principle		Diffuse reflection sensor
Application		For applications in robotics, assembly and handling technology
Electrical data		
Operating voltage	[V]	10...30 DC; (UL - Class 2 source required)
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Outputs		
Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	750
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Monitoring range		
Range	[mm]	5...30; (white paper 200 x 200 mm)
Range on white object (90 % remission)	[mm]	5...30

O7H200



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS

Range on grey object (18 % remission)	[mm]	6...30
Range on black object (6 % remission)	[mm]	7...29
Range adjustable		no
Max. light spot diameter	[mm]	2.5
Light spot dimensions refer to		at maximum range
Background suppression available		yes

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	1610

Mechanical data

Weight	[g]	14.4
Housing		rectangular
Dimensions	[mm]	20.3 x 15 x 9
Material		housing: PA
Lens material		front lens: PMMA
Lens alignment		Side sensing
Tightening torque	[Nm]	0.5

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm²

Connector: 1 x M8; coding: A; Contacts: 3; Locking: snap-fit



O7H200



Diffuse reflection sensors with background suppression

O7H-HPKG/0,20M/AS

Connection

