
TT2291

Temperature probe sensor

TT-250KFED06- /US/



L = probe length corresponds to installation length EL

EC 1935/2004 FCM CN FCM JP

Product characteristics			
Measuring range		-40...150 °C	-40...302 °F
Process connection		clamp adapter Ø 6 mm	
Installation length EL	[mm]	250	
Application			
Special feature		Gold-plated contacts	
Measuring element		1 x Pt 100; (to DIN EN 60751, class A)	
Application		hygienic systems	
Media		liquids and gases	
Pressure rating		160 bar	16 MPa
Minimum installation depth	[mm]	15	
Electrical data			
Protection class		III	
Measuring/setting range			
Probe length L	[mm]	250	
Measuring range		-40...150 °C	-40...302 °F
Accuracy / deviations			
Accuracy	[K]	± (0,15 K + 0,002 x|t|)	
Response times			
Dynamic response T05 / T09	[s]	1 / 3; (to DIN EN 60751)	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 68; IP 69K	
Tests / approvals			
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	22831	
UL approval		UL approval no.	K004
		File number UL	E217884
Mechanical data			
Weight	[g]	50.7	

TT2291

Temperature probe sensor

TT-250KFED06- /US/

Housing		cylindrical
Dimensions	[mm]	Ø 6 / L = 274
Materials		stainless steel (316L/1.4404)
Materials (wetted parts)		stainless steel (316L/1.4404) electropolished
Process connection		clamp adapter Ø 6 mm
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.8 µm
Probe diameter	[mm]	6
Installation length EL	[mm]	250

Remarks

Remarks	operating voltage "supply class 2" according to cULus
	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

