
PG2454

Pressure sensor with analogue display

PG-010-REB12-MFRKG/US/ /P

phase-out article

Alternative articles: PG1404
When selecting an alternative article and accessories please note that technical data may differ!



1 analogue display
2 alphanumeric display 4-digit
3 sensor field (programming button)

Product characteristics			
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1		
Measuring range	-1...10 bar	-14.4...145 psi	
Process connection	threaded connection G 1/2 external thread		
Application			
Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	-25...80		
Min. burst pressure	150 bar	2175 psi	15 MPa
Pressure rating	50 bar	725 psi	5 MPa
Type of pressure	relative pressure; vacuum		

PG2454

Pressure sensor with analogue display

PG-010-REB12-MFRKG/US/ /P

MAWP for applications according to CRN		38 bar	551 psi
Electrical data			
Operating voltage	[V]	18...32 DC	
Current consumption	[mA]	< 70; (24 V)	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	6	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analogue signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		1	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	75	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20, invertible; (scalable)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		-1...10 bar	-14.4...145 psi
Set point SP		-0.96...16 bar	-14...232 psi
Reset point rP		-1...15.96 bar	-14.4...231.6 psi
Analogue start point		-1...13.5 bar	-14.4...195.8 psi
Analogue end point		1.5...16 bar	21.8...232 psi
In steps of		0.02 bar	0.2 psi
Accuracy / deviations			
Switch point accuracy	[% of the span]	< ± 0,5; (Turn down 1:1)	
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (Turn down 1:1; BFSL = Best Fit Straight Line)	
Hysteresis deviation	[% of the span]	< ± 0,25; (Turn down 1:1)	
Long-term stability		< ± 0,1; (Turn down 1:1; per 6 months)	

PG2454

Pressure sensor with analogue display

PG-010-REB12-MFRKG/US/ /P

[% of the span]			
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,2; (0...70 °C)	
Temperature coefficient span [% of the span / 10 K]		< ± 0,2; (0...70 °C)	
Response times			
Response time [ms]		< 9	
Damping process value dAP [s]		0.01...30	
Damping for the analogue output dAA [s]		0.01...30	
Step response time analogue output [ms]		28	
Operating conditions			
Ambient temperature [°C]		-20...80	
Storage temperature [°C]		-40...100	
Protection		IP 67; IP 69K	
Tests / approvals			
EMC	DIN EN 61000-6-2		
	DIN EN 61000-6-3		
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)	
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)	
MTTF [years]		103	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight [g]		565.1	
Dimensions [mm]		169 x 100 x 57	
Materials		stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm	
Materials (wetted parts)		Al2O3 (ceramics); FKM; stainless steel (316L/1.4404)	
Min. pressure cycles		100 million	
Process connection		threaded connection G 1/2 external thread	
Restrictor element integrated		no (can be retrofitted)	
Displays / operating elements			
Display	Display unit	2 x LED, green	
	switching status	LED, yellow	
	switch points	LED ring, red	
	function display	alphanumeric display, red 4-digit	
	measured values	analogue display, 0...350° rotatable, pointer not visible when unit disconnected	
	measured values	alphanumeric display, red 4-digit	
With scale		yes	
Extended display range (max.)	16 bar	232 psi	
Remarks			
Remarks		switch point accuracy in the extended display range: 1.5 % of the span	
Pack quantity		1 pcs.	

PG2454

Pressure sensor with analogue display


PG-010-REB12-MFRKG/US/ /P


Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection





OUT1	switching output
OUT2	analogue output