


SM9604



Magnetic-inductive flow meter

SMN32XGX50KG/US-100



CE PA CRN cUL US LISTED EC 1935/2004 FCM JP UK CA

Product characteristics

Number of inputs and outputs	Number of analog outputs: 2			
Measuring range	5...300 l/min	0.3...18 m³/h	80...4755 gph	1.3...79.3 gpm
Process connection	threaded connection 1 1/2" NPT Internal thread DN40			

Application

Special feature	gold-plated contacts
Application	empty pipe detection; for industrial applications
Media	Conductive liquids; water; water-based media
Note on media	conductivity: ≥ 20 µS/cm
	viscosity: < 70 mm²/s (40 °C)

SM9604



Magnetic-inductive flow meter

SMN32XGX50KG/US-100

Medium temperature	-10...90 °C		14...194 °F	
Pressure rating	16 bar	232 psi	1.6 MPa	
MAWP (for applications according to CRN)	8.9 bar		0.89 MPa	

Electrical data	
Operating voltage [V]	18...32 DC; (to SELV/PELV)
Current consumption [mA]	< 150
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	5
Measuring principle	magnetic-inductive

Inputs / outputs	
Number of inputs and outputs	Number of analog outputs: 2

Outputs	
Total number of outputs	2
Output signal	analog signal
Number of analog outputs	2
Analog current output [mA]	4...20; (≤ 22 mA)
Max. load [Ω]	500

Measuring/setting range				
Measuring range	5...300 l/min	0.3...18 m ³ /h	80...4755 gph	1.3...79.3 gpm
Display range	-360...360 l/min	-21.6...21.6 m ³ /h	-5705...5705 gph	-95.1...95.1 gpm
Resolution	0.5 l/min	0.02 m ³ /h	5 gph	0.1 gpm
Analog start point ASP	0...240 l/min	0...14.4 m ³ /h	0...3800 gph	0...63.4 gpm
Analog end point AEP	60...300 l/min	3.6...18 m ³ /h	955...4755 gph	15.9...79.3 gpm
Low flow cut-off LFC	< 15 l/min	< 0.9 m ³ /h	< 240 gph	< 4 gpm
In steps of	0.5 l/min	0.02 m ³ /h	5 gph	0.1 gpm
Measuring dynamics	1:60			

Temperature monitoring		
Measuring range	-20...80 °C	-4...176 °F
Display range	-40...100 °C	-40...212 °F
Resolution	0.2 °C	0.5 °F
Analog start point	-20...60 °C	-4...140 °F
Analog end point	0...80 °C	32...176 °F
In steps of	0.2 °C	0.5 °F

Accuracy / deviations	
Flow monitoring	
Accuracy (in the measuring range)	$\pm (0,8 \% \text{ MW} + 0,5 \% \text{ MEW})$
Repeatability	$\pm 0,2\% \text{ MEW}$
Temperature monitoring	
Temperature drift	$\pm 0,0333 \text{ }^{\circ}\text{C} / \text{K}; \pm 0,0599 \text{ }^{\circ}\text{F} / \text{K}$
Accuracy [K]	$\pm 1 (25 \text{ }^{\circ}\text{C}; Q > 15 \text{ l/min}) / \pm 1 (77 \text{ }^{\circ}\text{F}; Q > 4 \text{ gpm})$

SM9604



Magnetic-inductive flow meter

SMN32XGX50KG/US-100

Reaction times		
Flow monitoring		
Response time	[s]	0.35; (dAP = 0)
Damping process value dAP	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 3 (Q > 15 l/min) / T09 = 3 (Q > 4 gpm)
Software / programming		
Parameter setting options	display can be deactivated; Display unit; empty pipe detection	
Operating conditions		
Ambient temperature	-10...60 °C	14...140 °F
Storage temperature	-25...80 °C	-13...176 °F
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 60947-5-9	
	DIN EN 61000-6-2	
CPA approval	model number	003MI
	accuracy class	-
	maximum allowable error	± 1,5 % FS
	Q (min)	0,3 m³/h
	Q (t)	-
	Q (max)	18 m³/h
	Medium temperature	-10...70 °C
	Medium temperature	14...158 °F
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	85
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	2745
Housing	rectangular	
Inlet pipe length	3 x DN	
Outlet pipe length	1 x DN	
Dimensions	[mm]	170 x 103 x 117
Material	stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); PEI; FKM; PBT-GF20; TPE-U	
Materials (wetted parts)	stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); PEEK; FKM	
Process connection	threaded connection 1 1/2" NPT Internal thread DN40	
Displays / operating elements		
Display	Display unit	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F
	Function display	1 x LED, yellow (10³)
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit
Display unit	l/min; m³/h; gpm; gph; °C; °F	
Accessories		
Items supplied	Label	

SM9604



Magnetic-inductive flow meter

SMN32XGX50KG/US-100


Remarks	
Remarks	MW = Measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



OUT1: Colors to DIN EN 60947-5-2
OUT2: analog output Temperature monitoring
analog output Volumetric flow quantity monitoring
Core colors :
BK = black
BN = brown
BU = blue
WH = white

SM9604




Magnetic-inductive flow meter

SMN32XGX50KG/US-100

Diagrams and graphs

Pressure loss



dP Pressure loss
Q volumetric flow quantity