
E20633

Fibre optic diffuse reflection sensor

FT-11-EPA-M6/F2X1/2M



Application		
Function principle		Diffuse reflection sensor
Application		For use in industrial environments
Detection zone		
Range with fibre optic amplifier type		OB50; OBF; OCF; OO50
OB50		
Range fibre optics	[mm]	70
OBF		
Range fibre optics	[mm]	100
OCF (High Power)		
Range fibre optics	[mm]	1250
OO50		
Range fibre optics	[mm]	300
Operating conditions		
Ambient temperature	[°C]	-40...70
Mechanical data		
Weight	[g]	48.5
Version of sensing head		straight
Sensing head thread		M6

E20633

Fibre optic diffuse reflection sensor

FT-11-EPA-M6/F2X1/2M

Sensing head length	[mm]	35
Total length	[mm]	2000
Min. bending radius	[mm]	30
Fibre arrangement		
Core diameter	[mm]	2 x 1
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE
Accessories		
Items supplied		hexagon nuts: 2 x M6 (3,1 mm), stainless steel
		tooth lock washers: 2
Accessories (optional)		Cutter for fibre optics:, E20600
Remarks		
Pack quantity		1 pcs.